
























Breast Pump	Ideal for the mom...	Performance	Ease of Use	Comfort	Battery	Noise Level
 <p>Symphony PLUS[®] Hospital Grade Double Electric Breast Pump (multi-user)</p>	<p>...who needs to INITIATE & BUILD her milk supply from the very beginning. Best for moms of multiples and preemies. Available for rent. Use: frequent, daily</p>	<p>Initiation Technology™ 2-Phase Expression[®] Technology Optimized speed/suction levels</p>	<p>Closed system Simple switch between Initiation & Maintain Programs #1 pump used in Canadian Hospitals</p>	<p>Symphony Pumping Kit with PersonalFit PLUS Breast Shields (2 x 24mm)</p>	 No battery	 Quiet
 <p>Sonata[®] Double Electric Breast Pump</p>	<p>... who is looking for a pump that features hospital inspired performance, connectivity & two clinically tested rhythms Use: frequent, daily</p>	<p>Auto-adjusts suction via Responsive Pump Technology™ 2-Phase Expression[®] Technology Optimized speed/suction levels</p>	<p>Closed system Self-troubleshoots & alerts Auto-uploads pumping sessions to MyMedela App Few parts, easy to clean & assemble</p>	 PersonalFit Flex Breast Shields 2 x 21 mm – 2 x 24 mm	 Rechargeable	 Very quiet
 <p>Freestyle Flex™ Double Electric Breast Pump</p>	<p>...who wants to pump anytime, anywhere with a fully mobile, connected pump Use: frequent, daily</p>	<p>Consistent suction strength while mobile 2-Phase Expression[®] Technology Optimized speed/suction levels</p>	<p>Closed system Lightweight & compact Auto-uploads pumping sessions to MyMedela App Few parts, easy to clean & assemble</p>	 PersonalFit Flex Breast Shields 2 x 21 mm – 2 x 24 mm	 Rechargeable	 Quiet
 <p>Pump In Style[®] Double Electric Breast Pump</p>	<p>... who is looking for a highly effective, easy to use breast pump Use: frequent, daily</p>	<p>MaxFlow™ Technology with micro-vibrations 2-Phase Expression[®] Technology Optimized speed/suction levels</p>	<p>Closed system 4 easy to use push buttons Few parts, easy to clean & assemble</p>	 PersonalFit Flex Breast Shields 2 x 21 mm – 2 x 24 mm	 Up to 2hrs 8 x AA	 Moderate
 <p>Swing[®] Single Electric Breast Pump</p>	<p>...who wants a small, versatile sidekick to complement her breastfeeding routine Use: 3-5 sessions/week</p>	<p>2-Phase Expression[®] Technology Optimized speed/suction levels</p>	<p>Can use while breastfeeding 4 easy to use push buttons Few parts, easy to clean & assemble</p>	 PersonalFit Breast Shield 1 x 24mm	 Up to 3hrs 8 x AA	 Quiet
 <p>Harmony[®] Manual Breast Pump</p>	<p>...who is primarily breastfeeding and wants to express/collect her milk with an easy to use pump Use: 5-10 sessions/month</p>	<p>2-Phase Expression[®] Technology</p>	<p>Can use while breastfeeding Manual control of speed/suction Few parts, easy to clean & assemble Dishwasher safe</p>	 PersonalFit Flex Breast Shield 1 x 24mm	 Manual	 Very quiet

Note: Battery life may vary due to suction settings, environmental factors and types of batteries used. Content appearance may vary from picture. Contents included may vary by breast pump model. Medela wordmark and logo, Symphony PLUS, Sonata, Pump in Style, Swing, Harmony, and 2-Phase Expression are registered in the U.S. Patent and Trademark Office. Freestyle Flex, PersonalFit, PersonalFit Flex, Initiation Technology, and MaxFlow are trademarks of Medela.